



































































LEONARDO SIMBOLI E INDIRIZZI ELETTRICI	
<p>1  2  3  4  5  6  7  8  9  10  11  12  13  14  15  16  17  18  19  20  21  22  23  24  25  26  27  28  29  30  31  32  33  34  35  36  37  38  39  40  41  42  43  44  45  46  47  48  49  50  51  52  53  54  55  56  57  58  59  60  61  62  63  64  65  66  67 68 69 70 71 72 73 74 75 76 77 78 79 80 81 82 83 84 85 86 87 </p>	

The image is a detailed architectural floor plan of a building, likely a school or office. The plan shows various rooms, corridors, and technical specifications. Key features include:

- Rooms and Areas:** The plan is divided into several rooms, some of which are highlighted with red rectangular borders. These rooms contain various pieces of furniture and equipment, including desks, chairs, and storage units.
- Dimensions:** Numerous dimensions are provided throughout the plan, indicating the size of rooms, corridors, and specific areas. These dimensions are given in meters (m).
- Technical Specifications:** The plan includes various technical specifications and labels, such as "K418 E", "K418 F", "K418 G", "K418 H", "K418 I", "K418 J", "K418 K", "K418 L", "K418 M", "K418 N", "K418 O", "K418 P", "K418 Q", "K418 R", "K418 S", "K418 T", "K418 U", "K418 V", "K418 W", "K418 X", "K418 Y", "K418 Z", "K418 AA", "K418 AB", "K418 AC", "K418 AD", "K418 AE", "K418 AF", "K418 AG", "K418 AH", "K418 AI", "K418 AJ", "K418 AK", "K418 AL", "K418 AM", "K418 AN", "K418 AO", "K418 AP", "K418 AQ", "K418 AR", "K418 AS", "K418 AT", "K418 AU", "K418 AV", "K418 AW", "K418 AX", "K418 AY", "K418 AZ", "K418 BA", "K418 BB", "K418 BC", "K418 BD", "K418 BE", "K418 BF", "K418 BG", "K418 BH", "K418 BI", "K418 BJ", "K418 BK", "K418 BL", "K418 BM", "K418 BN", "K418 BO", "K418 BP", "K418 BQ", "K418 BR", "K418 BS", "K418 BT", "K418 BU", "K418 BV", "K418 BW", "K418 BX", "K418 BY", "K418 BZ", "K418 CA", "K418 CB", "K418 CC", "K418 CD", "K418 CE", "K418 CF", "K418 CG", "K418 CH", "K418 CI", "K418 CJ", "K418 CK", "K418 CL", "K418 CM", "K418 CN", "K418 CO", "K418 CP", "K418 CQ", "K418 CR", "K418 CS", "K418 CT", "K418 CU", "K418 CV", "K418 CW", "K418 CX", "K418 CY", "K418 CZ", "K418 DA", "K418 DB", "K418 DC", "K418 DD", "K418 DE", "K418 DF", "K418 DG", "K418 DH", "K418 DI", "K418 DJ", "K418 DK", "K418 DL", "K418 DM", "K418 DN", "K418 DO", "K418 DP", "K418 DQ", "K418 DR", "K418 DS", "K418 DT", "K418 DU", "K418 DV", "K418 DW", "K418 DX", "K418 DY", "K418 DZ", "K418 EA", "K418 EB", "K418 EC", "K418 ED", "K418 EE", "K418 EF", "K418 EG", "K418 EH", "K418 EI", "K418 EJ", "K418 EK", "K418 EL", "K418 EM", "K418 EN", "K418 EO", "K418 EP", "K418 EQ", "K418 ER", "K418 ES", "K418 ET", "K418 EU", "K418 EV", "K418 EW", "K418 EX", "K418 EY", "K418 EZ", "K418 FA", "K418 FB", "K418 FC", "K418 FD", "K418 FE", "K418 FF", "K418 FG", "K418 FH", "K418 FI", "K418 FJ", "K418 FK", "K418 FL", "K418 FM", "K418 FN", "K418 FO", "K418 FP", "K418 FQ", "K418 FR", "K418 FS", "K418 FT", "K418 FU", "K418 FV", "K418 FW", "K418 FX", "K418 FY", "K418 FZ", "K418 GA", "K418 GB", "K418 GC", "K418 GD", "K418 GE", "K418 GF", "K418 GG", "K418 GH", "K418 GI", "K418 GJ", "K418 GK", "K418 GL", "K418 GM", "K418 GN", "K418 GO", "K418 GP", "K418 GQ", "K418 GR", "K418 GS", "K418 GT", "K418 GU", "K418 GV", "K418 GW", "K418 GX", "K418 GY", "K418 GZ", "K418 HA", "K418 HB", "K418 HC", "K418 HD", "K418 HE", "K418 HF", "K418 HG", "K418 HH", "K418 HI", "K418 HJ", "K418 HK", "K418 HL", "K418 HM", "K418 HN", "K418 HO", "K418 HP", "K418 HQ", "K418 HR", "K418 HS", "K418 HT", "K418 HU", "K418 HV", "K418 HW", "K418 HX", "K418 HY", "K418 HZ", "K418 IA", "K418 IB", "K418 IC", "K418 ID", "K418 IE", "K418 IF", "K418 IG", "K418 IH", "K418 II", "K418 IJ", "K418 IK", "K418 IL", "K418 IM", "K418 IN", "K418 IO", "K418 IP", "K418 IQ", "K418 IR", "K418 IS", "K418 IT", "K418 IU", "K418 IV", "K418 IW", "K418 IX", "K418 IY", "K418 IZ", "K418 JA", "K418 JB", "K418 JC", "K418 JD", "K418 JE", "K418 JF", "K418 JG", "K418 JH", "K418 JI", "K418 JJ", "K418 JK", "K418 JL", "K418 JM", "K418 JN", "K418 JO", "K418 JP", "K418 JQ", "K418 JR", "K418 JS", "K418 JT", "K418 JU", "K418 JV", "K418 JW", "K418 JX", "K418 JY", "K418 JZ", "K418 KA", "K418 KB", "K418 KC", "K418 KD", "K418 KE", "K418 KF", "K418 KG", "K418 KH", "K418 KI", "K418 KJ", "K418 KK", "K418 KL", "K418 KM", "K418 KN", "K418 KO", "K418 KP", "K418 KQ", "K418 KR", "K418 KS", "K418 KT", "K418 KU", "K418 KV", "K418 KW", "K418 KX", "K418 KY", "K418 KZ", "K418 LA", "K418 LB", "K418 LC", "K418 LD", "K418 LE", "K418 LF", "K418 LG", "K418 LH", "K418 LI", "K418 LJ", "K418 LK", "K418 LL", "K418 LM", "K418 LN", "K418 LO", "K418 LP", "K418 LQ", "K418 LR", "K418 LS", "K418 LT", "K418 LU", "K418 LV", "K418 LW", "K418 LX", "K418 LY", "K418 LZ", "K418 MA", "K418 MB", "K418 MC", "K418 MD", "K418 ME", "K418 MF", "K418 MG", "K418 MH", "K418 MI", "K418 MJ", "K418 MK", "K418 ML", "K418 MM", "K418 MN", "K418 MO", "K418 MP", "K418 MQ", "K418 MR", "K418 MS", "K418 MT", "K418 MU", "K418 MV", "K418 MW", "K418 MX", "K418 MY", "K418 MZ", "K418 NA", "K418 NB", "K418 NC", "K418 ND", "K418 NE", "K418 NF", "K418 NG", "K418 NH", "K418 NI", "K418 NJ", "K418 NK", "K418 NL", "K418 NM", "K418 NN", "K418 NO", "K418 NP", "K418 NQ", "K418 NR", "K418 NS", "K418 NT", "K418 NU", "K418 NV", "K418 NW", "K418 NX", "K418 NY", "K418 NZ", "K418 OA", "K418 OB", "K418 OC", "K418 OD", "K418 OE", "K418 OF", "K418 OG", "K418 OH", "K418 OI", "K418 OJ", "K418 OK", "K418 OL", "K418 OM", "K418 ON", "K418 OO", "K418 OP", "K418 OQ", "K418 OR", "K418 OS", "K418 OT", "K418 OU", "K418 OV", "K418 OW", "K418 OX", "K418 OY", "K418 OZ", "K418 PA", "K418 PB", "K418 PC", "K418 PD", "K418 PE", "K418 PF", "K418 PG", "K418 PH", "K418 PI", "K418 PJ", "K418 PK", "K418 PL", "K418 PM", "K418 PN", "K418 PO", "K418 PP", "K418 PQ", "K418 PR", "K418 PS", "K418 PT", "K418 PU", "K418 PV", "K418 PW", "K418 PX", "K418 PY", "K418 PZ", "K418 QA", "K418 QB", "K418 QC", "K418 QD", "K418 QE", "K418 QF", "K418 QG", "K418 QH", "K418 QI", "K418 QJ", "K418 QK", "K418 QL", "K418 QM", "K418 QN", "K418 QO", "K418 QP", "K418 QQ", "K418 QR", "K418 QS", "K418 QT", "K418 QU", "K418 QV", "K418 QW", "K418 QX", "K418 QY", "K418 QZ", "K418 RA", "K418 RB", "K418 RC", "K418 RD", "K418 RE", "K418 RF", "K418 RG", "K418 RH", "K418 RI", "K418 RJ", "K418 RK", "K418 RL", "K418 RM", "K418 RN", "K418 RO", "K418 RP", "K418 RQ", "K418 RR", "K418 RS", "K418 RT", "K418 RU", "K418 RV", "K418 RW", "K418 RX", "K418 RY", "K418 RZ", "K418 SA", "K418 SB", "K418 SC", "K418 SD", "K418 SE", "K418 SF", "K418 SG", "K418 SH", "K418 SI", "K418 SJ", "K418 SK", "K418 SL", "K418 SM", "K418 SN", "K418 SO", "K418 SP", "K418 SQ", "K418 SR", "K418 SS", "K418 ST", "K418 SU", "K418 SV", "K418 SW", "K418 SX", "K418 SY", "K418 SZ", "K418 TA", "K418 TB", "K418 TC", "K418 TD", "K418 TE", "K418 TF", "K418 TG", "K418 TH", "K418 TI", "K418 TJ", "K418 TK", "K418 TL", "K418 TM", "K418 TN", "K418 TO", "K418 TP", "K418 TQ", "K418 TR", "K418 TS", "K418 TT", "K418 TU", "K418 TV", "K418 TW", "K418 TX", "K418 TY", "K

[illegible]

A.S.L. n°4 - LANUSEI
PRESIDIO OSPEDALIERO
"NOSTRA SIGNORA DELLE MERCEDE" DI LANUSEI

DATA: (UNIST)	Febbraio 2016
<p>Pianta Piano Terra - Reparto Pronto Soccorso Impianti elettrici, di sicurezza e speciali In bassissima tensione Topografia apparecchi terminali ed utilizzatori scala 1:50</p>	
<p>ELE 1</p>	

2. RULE: GEOM. CONGRUENCE STATEMENTS

AREA OGGETTO DI INTERVENTO

AREA NON OGGETTO DI INTERVENTO
CON IL PRESENTE LOTTO

Technical drawing of a wall-mounted cabinet with dimensions and callouts:

- Top Section:**
 - Callout 1: 10
 - Callout 2: 10
 - Callout 3: 100
 - Callout 4: 2.25
 - Callout 5: 2.25
 - Callout 6: 150
 - Callout 7: 150
 - Callout 8: 100
 - Callout 9: 130
- Bottom Section:**
 - Callout 10: 30
 - Callout 11: 30
 - Callout 12: 140
 - Callout 13: 30

Dimensions are indicated by red arrows. Callouts are numbered 1 through 13. The drawing includes a vertical hatched line on the left representing the wall and a horizontal line at the bottom representing the floor.

Technical drawing of a wall-mounted unit. The unit is shown in profile, mounted on a wall. The drawing includes a side view of the unit and a top-down view of the control panel. The control panel features a digital display, several buttons, and a power switch. A dimension line indicates a distance of 110 units from the wall to the center of the control panel. The text "P.L.O. PAVIMENTO FINITO" is written vertically on the left side of the drawing.